

Fire Door Kit E

a brand of **HOPPE® GROUP**

Office Door Locking



APPLICATION

For use on office, meeting, classroom, type doors. Lever handle operates a latch bolt. Cylinder and turn operates a deadbolt. Suitable for FD30 and FD60 timber doors.

COMPONENT

CERTIFIRE

Ball Bearing Grade 13 Hinges	1.5pr	CF369
Intumescent pack for hinges	1 pack of 6	CF369
Euro mortice UK sashlock, 76mm, SC	1	CF577
Intumescent pack for sashlock	1	CF577
Overhead door closer, size 2-4, silver	1	CF603
Fire Door Keep Shut sign SS	2	N/A
Euro cylinder & turn, 5-pin, 70mm, c/w 3 keys, SC	1	N/A
Lever handles, return to door, Grade 304 SS	1 set	N/A
Euro profile escutcheon Grade 304 SS	1 pr	N/A

TECHNICAL

Max door weight 80kg (60kg Fig6), max door width 1100mm (950mm Fig6)

Sashlock - Grade 2 - Medium frequency use, e.g. internal office doors

Lever handles - Satisfy BS8300:2009, with bolt through fixings.

Door closer - Size 2-4 adjustment by template, separate closing speed and latch action adjustment

BENEFITS

All products from one manufacturer ensures users confidence in compatibility, functionality and after-sales support

UK size sashlock with square faceplate, plus square cornered hinges, provide easier and quicker on-site installation

All products are backed by HOPPE's 5 year guarantee on mechanical operation, subject to T&C's