

PDU-12WS-V

12-Way Vertical
Non-Surged Protected
PDU



Telecom &
Networking



Data centres &
Server farms



Broadcast &
A/V



HVAC &
Industrial

Cost-Effective Power Distribution For Your Applications

Need a competitively priced but quality Power Distribution Unit (PDU) for your applications or installation?

The new **PDU-12WS-V** is a robust, non-surged protected PDU which features effective electrical distribution to its integral, 12-way, UK-socketed 3-pin sockets.

Combining a fully certified UK plug input combined with a compatible heavy load power flex means you can be assured this LMS Data PDU can work without problems, 24/7.

Ideal for data, telco and broadcast applications, with the added benefit of a low-profile, 1U high and the ability to be mounted vertically in almost all floor, telco and server enclosures via the standard mount slots.

Robust in design, with an integral neon illuminated rocker switch for assured functionality, the LMS Data PDU is designed to deliver maximum electrical power - today and tomorrow.

specifications:

Vertical, high-density Power Distribution Unit (PDU)

UK-plug style plug power input

12-Way UK, 3-Pin Power Outlets

Robust, black aluminium design for industrial use

Neon on/off power switch for assured control

Maximum power rating - 4000W (approx.)

1.8 metre (approx.) power cordage

Ideal for data, telecom, broadcast and HVAC applications



* Image for representation only
Subject to change



Copyright 2017 LMS Data
All trademarks acknowledged E&OE.
Details subject to change