

# Power module - EMD-SL-PS- 24AC - 2866103

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Power modules, pluggable, for EMD-SL-..., supply voltage: 20.2...26.4 V AC

## Your advantages

- Separately adjustable startup and response delays
- Variable supply voltage range
- Adjustable via potentiometer on the front



## Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| GTIN                                 | <br>4 017918 952709 |
| GTIN                                 | 4017918952709   |
| Weight per Piece (excluding packing) | 46.400 g  |
| Custom tariff number                 | 85043180  |
| Country of origin                    | Germany   |

## Technical data

### Dimensions

|        |       |
|--------|-------|
| Width  | 32 mm |
| Height | 35 mm |
| Depth  | 16 mm |

### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)         | -25 °C ... 55 °C |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |

### Input data

|                       |                    |
|-----------------------|--------------------|
| Nominal input voltage | 24 V AC (50/60 Hz) |
|-----------------------|--------------------|

### Environmental Product Compliance

# Power module - EMD-SL-PS- 24AC - 2866103

## Technical data

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27040600 |
| eCl@ss 4.1 | 27040600 |
| eCl@ss 5.0 | 27049200 |
| eCl@ss 5.1 | 27049200 |
| eCl@ss 6.0 | 27049000 |
| eCl@ss 7.0 | 27049002 |
| eCl@ss 8.0 | 27049002 |
| eCl@ss 9.0 | 27040701 |

### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC002540 |
| ETIM 5.0 | EC002540 |
| ETIM 6.0 | EC002540 |
| ETIM 7.0 | EC002540 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211916 |
| UNSPSC 7.0901 | 39121535 |
| UNSPSC 11     | 39121535 |
| UNSPSC 12.01  | 39121535 |
| UNSPSC 13.2   | 39121004 |
| UNSPSC 18.0   | 39121004 |
| UNSPSC 19.0   | 39121004 |
| UNSPSC 20.0   | 39121004 |
| UNSPSC 21.0   | 39121004 |

## Approvals

### Approvals

---

Approvals

EAC

---


Ex Approvals

## Power module - EMD-SL-PS- 24AC - 2866103

### Approvals

---

#### Approval details

|     |   |                           |
|-----|---|---------------------------|
| EAC |  | RU *-<br>DE. **08.B-02133 |
|-----|---|---------------------------|

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>