

## Hose holder with cover - WP-BASE C PA HF 10,0 BK - 3240958


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Hose holder with cover

RoHS

### Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710657
GTIN	4046356710657
Weight per Piece (excluding packing)	3.880 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Hole diameter	5.5 mm
Diameter	10 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

#### General

Color	black
Components	halogen-free
Flammability rating according to UL 94	V2
Material	PA

#### Standards and Regulations

Connection in acc. with standard	UL
----------------------------------	----

# Hose holder with cover - WP-BASE C PA HF 10,0 BK - 3240958

## Technical data

### Standards and Regulations

Flammability rating according to UL 94	V2
----------------------------------------	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	23159090
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27439208
eCl@ss 8.0	27439208
eCl@ss 9.0	23159090

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000127
ETIM 5.0	EC001171
ETIM 6.0	EC001171
ETIM 7.0	EC000368

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411
UNSPSC 18.0	31162906
UNSPSC 19.0	31162906
UNSPSC 20.0	31162906
UNSPSC 21.0	31162906

## Approvals

### Approvals

## Hose holder with cover - WP-BASE C PA HF 10,0 BK - 3240958

### Approvals

Approvals

UL Recognized

---

Ex Approvals

---

### Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

### Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 10,0 BK - 3240680



Polyamide protective hose, inflammability class V0, UV resistant

---

Protective hose - WP-PA HF-HB 10,0 BK - 3240838



Polyamide protective hose, inflammability class HB, UV resistant

---