

Cable protection end sleeve - WP-SC PA HF 10,0 BK - 3240981

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End sleeves as cable protection

RoHS

Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710992
GTIN	4046356710992
Weight per Piece (excluding packing)	1.030 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	20 mm
Diameter	10 mm
Inner diameter (f)	4.3 mm
Outside diameter	10 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	black
Components	halogen-free
Flammability rating according to UL 94	V2
Material	PA

Cable protection end sleeve - WP-SC PA HF 10,0 BK - 3240981

Technical data

Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	V2

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27430316
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27439210
eCl@ss 8.0	27439210
eCl@ss 9.0	27430316

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC000519
ETIM 6.0	EC000519
ETIM 7.0	EC000519

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121404
UNSPSC 18.0	39121404
UNSPSC 19.0	39121404
UNSPSC 20.0	39121404
UNSPSC 21.0	39121404

Approvals

Approvals

Cable protection end sleeve - WP-SC PA HF 10,0 BK - 3240981

Approvals

Approvals

LR / UL Recognized

Ex Approvals

Approval details

LR



<http://www.lr.org/en>

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>
