

Blind rivet - RVT-AL/ST 4,8/12 - 3240521

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Blind rivets, Ø 4.8 mm, 12 mm sleeve length, aluminum sleeve, zinc-plated steel pin, flat head, standard version similar to DIN 7337 A

Your advantages

- ✓ Special rivets are available for fixing RW... and UW... high-current panel feed-through terminal blocks that are specifically designed for terminal blocks
- ✓ Compact, ergonomically shaped pliers
- ✓ 3 inserts for rivet diameter of 2.4 - 3.2 mm, 4 mm, and 4.8 - 5.0 mm

Key Commercial Data

Packing unit	500 pc
Minimum order quantity	500 pc
GTIN	 4 046356 527521
GTIN	4046356527521
Weight per Piece (excluding packing)	2.820 g
Custom tariff number	83082000
Country of origin	China
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	12 mm
Hole diameter	4.9 mm
Diameter	4.8 mm
Max. material thickness	8 mm
Material thickness (g)	6 mm

General

Color	silver
-------	--------

Blind rivet - RVT-AL/ST 4,8/12 - 3240521

Technical data

General

Material	Aluminum (AlMg 3/3.5)/galvanized steel
----------	--

Classifications

eCl@ss

eCl@ss 10.0.1	23120402
eCl@ss 4.0	21043074
eCl@ss 4.1	21043074
eCl@ss 5.0	23120402
eCl@ss 5.1	23120400
eCl@ss 6.0	23120400
eCl@ss 7.0	23120402
eCl@ss 8.0	23120402
eCl@ss 9.0	23120402

ETIM

ETIM 3.0	EC002339
ETIM 4.0	EC002339
ETIM 5.0	EC002339
ETIM 6.0	EC002339
ETIM 7.0	EC002339

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	31162201
UNSPSC 19.0	31162201