

Sample set - URTK/S VT-TERMINAL GROUP - 3030064

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The set consists of the following: 8 x URTK/S, 2 x UK 6 N, 1 x D-UK 4/10, 1 x E/UK, 3 x USB 2-RTK/S, 3 x ATS-RTK, 1 x D-URTK, 1 x FB 10-RTK/S, 2 x ZB 8:UNBEDRUCKT

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4017918406127
Weight per Piece (excluding packing)	449.000 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Articles in set

Test disconnect terminal block - URTK/S - 0311087



Test disconnect terminal block, with two test sockets for 4 mm test plugs, or for receiving bridge bars or screw bridges, connection method: Screw connection, cross section: 0.5 mm² - 10 mm², AWG: 20 - 10, width: 8.2 mm, mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

Sample set - URTK/S VT-TERMINAL GROUP - 3030064

Articles in set

Feed-through terminal block - UK 6 N - 3004524



Feed-through terminal block, nom. voltage: 800 V, nominal current: 41 A, connection method: Screw connection, number of connections: 2, cross section: 0.2 mm² - 10 mm², AWG: 24 - 8, width: 8.2 mm, color: gray, mounting type: NS 35/7,5, NS 35/15, NS 32

End cover - D-UK 4/10 - 3003020



End cover, length: 42.5 mm, width: 1.8 mm, height: 35.9 mm, color: gray

End clamp - E/UK - 1201442



End clamp, width: 9.5 mm, height: 35.3 mm, material: PA, length: 50.5 mm, Mounting on a DIN rail NS 32 or NS 35, color: gray

Switching jumper - USB 2-RTK/S - 0311278



Switching jumper, pitch: 8.2 mm, number of positions: 2, color: silver

Partition plate - ATS-RTK - 0310224



Partition plate, length: 97.5 mm, width: 0.8 mm, height: 45.8 mm, color: gray

Sample set - URTK/S VT-TERMINAL GROUP - 3030064

Articles in set

Cover - D-URTK - 0310020



Cover, length: 72 mm, width: 2.2 mm, height: 41.5 mm, color: gray

Fixed bridge - FBI 10- 8 - 0203263



Fixed bridge, pitch: 8 mm, number of positions: 10, color: silver

Screw bridge - FB 10- RTK/S - 0311171



Screw bridge, pitch: 8.2 mm, number of positions: 10, color: silver

Zack marker strip - ZB 8:UNBEDRUCKT - 1052002



Zack marker strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, lettering field size: 10.5 x 8.15 mm, Number of individual labels: 10

Classifications

eCl@ss

eCl@ss 10.0.1	27149290
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141120
eCl@ss 8.0	27149290
eCl@ss 9.0	27149290

Sample set - URTK/S VT-TERMINAL GROUP - 3030064

Classifications

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897
ETIM 6.0	EC000897
ETIM 7.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410
UNSPSC 18.0	26121641
UNSPSC 19.0	26121641
UNSPSC 20.0	26121641
UNSPSC 21.0	26121641

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.BL08.B.00534
-----	---	--------------------------