

Cable adapter - GW HART USB MODEM - 1003824

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



USB HART modem cable for communication between a PC and HART devices, cable length: 1m.

Your advantages

- USB HART modem for commissioning, calibrating, and monitoring HART devices

Key Commercial Data

| | |
|--------------------------------------|---------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4055626472072 |
| Weight per Piece (excluding packing) | 70.000 g |
| Custom tariff number | 85444290 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--------------------|-----|
| Fixed cable length | 1 m |
|--------------------|-----|

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | 0 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

General

| | |
|-------------------|-------------------|
| Connection 1 | PC side |
| Connection method | USB 2.0 Fullspeed |
| Note | serial |
| Connection 2 | Device side |
| | USB type A (male) |
| Connection method | Minigrabber |

Cable adapter - GW HART USB MODEM - 1003824

Technical data

General

| | |
|---------------------|---|
| Number of positions | 2 |
|---------------------|---|

Standards and Regulations

| | |
|-------------------------------|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Noise emission | EN 55032 |
| Noise immunity | EN 55024 |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 19179290 |
| eCl@ss 6.0 | 19179200 |
| eCl@ss 7.0 | 19179290 |
| eCl@ss 9.0 | 19179290 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC002584 |
| ETIM 6.0 | EC000310 |
| ETIM 7.0 | EC000310 |