

Cutter - THERMOMARK ROLL-CUTTER - 5146422

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cutter for THERMOMARK ROLL and THERMOMARK ROLL 2.0, cutter width: 110 mm, suitable for: TML, SK, EML-RM, PMM, WMS, WMS-2 HF, WMS-OT HF, TMT continuous media, and EMT (EX15)R

Your advantages

- Custom length cuts of continuous markers



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 528559
GTIN	4046356528559
Weight per Piece (excluding packing)	579.900 g
Custom tariff number	82089000
Country of origin	Germany

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	19149290
eCl@ss 4.0	24010400
eCl@ss 4.1	24010400
eCl@ss 5.0	19020200
eCl@ss 5.1	19020200
eCl@ss 6.0	19149200

Cutter - THERMOMARK ROLL-CUTTER - 5146422

Classifications

eCl@ss

eCl@ss 7.0	19149290
eCl@ss 8.0	19149290
eCl@ss 9.0	19149290

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001675
ETIM 6.0	EC001675
ETIM 7.0	EC001675

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43211612
UNSPSC 18.0	43211612
UNSPSC 19.0	43211612
UNSPSC 20.0	43211612
UNSPSC 21.0	43211612