



Ultimate SU630 3D NAND SSD

If you're looking to replace that HDD of yours with an SSD, look no further than the ADATA SU630. The SSD is built with next-generation QLC 3D NAND Flash to offer amazing value and great performance. It also comes with excellent features such as LDPC ECC technology.

Features

- 3D QLC NAND Flash for higher affordability
- Big capacity up to 3.84TB
- Advanced hardware LDPC ECC technology
- Supports SLC Caching for improved performance
- Free software: SSD Toolbox and Migration Utility
- Supports S.M.A.R.T., TRIM Command, and NCQ

Ordering Information

Capacity	Model Number	EAN Code
240GB	ASU630SS-240GQ-R	4713218469175
480GB	ASU630SS-480GQ-R	4713218469182
960GB	ASU630SS-960GQ-R	4713218469199
1.92TB	ASU630SS-1T92Q-R	4710273773551
3.84TB	ASU630SS-3T84Q-R	4710273774169

Specifications

- Capacity: 240GB/ 480GB / 960GB / 1.92TB / 3.84TB
- NAND Flash: 3D QLC
- Interface: SATA 6Gb/s (SATA III)
- Form Factor: 2.5"
- Dimensions (L x W x H): 100.45 x 69.85 x 7mm
- Weight: 47.5g
- Operating Temperature: 0°C-70°C
- Storage Temperature: -40°C-85°C
- Shock Resistance: 1500G/0.5ms
- MTBF: 1,500,000 hours
- Certifications: RoHS, CE, FCC, BSMI, VCCI, KC
- Warranty: 3 years

Performance

Capacity	ATTO		CDM-QD32T1		AS SSD		4K Random		TBW
	Seq. Read (MB/s)	Seq. Write (MB/s)	Seq. Read (MB/s)	Seq. Write (MB/s)	Seq. Read (MB/s)	Seq. Write (MB/s)	Read (IOPS)	Write (IOPS)	
240GB	Up to 520	Up to 450	Up to 520	Up to 450	Up to 520	Up to 400	30K	65K	50TB
480GB	Up to 520	Up to 450	Up to 520	Up to 450	Up to 500	Up to 440	40K	65K	100TB
960GB	Up to 520	Up to 450	Up to 520	Up to 450	Up to 500	Up to 440	40K	65K	200TB
1.92TB	Up to 520	Up to 450	Up to 520	Up to 450	Up to 500	Up to 440	40K	65K	400TB
3.84TB	Up to 520	Up to 450	Up to 520	Up to 450	Up to 500	Up to 440	40K	65K	800TB

*Performance may vary based on SSD capacity, hardware test platform, test software, operating system, and other system variables

Schematics

