

Han 75DDD M-c



Part number	09 16 075 2001
Specification	Han 75DDD M-c
HARTING eCatalogue	https://b2b.harting.com/09160752001

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Series	Han [®] DDD

Version

Termination method	Crimp termination
Gender	Male
Size	10 B
Number of contacts	75
PE contact	Yes
Details	PE connection with a Han D [®] crimp contact Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 2.5 mm²
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500

Page 1 / 2 | Creation date 2020-02-18 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

Polycarbonate (PC)
RAL 7032 (pebble grey)
V-0
IEC 61984
1
1 g
China
85366990