

## 3-Port USB-C Hub with LAN Port, USB-C to 3x USB-A Ports and Gbe, USB 3.0, Black

MODEL NUMBER: **U460-003-3A1GB**



Adds 3 USB-A ports and a Gigabit Ethernet port to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

### Description

The U460-003-3A1GB USB 3.1 Gen 1 USB-C Portable Hub/Adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, charging a mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

The plug-and-play U460-003-3A1GB requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Three USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer. Each port supports USB Battery Charging (BC) specification v1.2, which indicates they provide up to 1.5A for fast charging of mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

### Features

**Turn Your Device's USB-C Port into a Workstation** Ideal for adding USB peripherals, powering a mobile device, and connecting to a Gigabit Ethernet network simultaneously  
**Plug-and-play operation with no software, drivers or external power required** White LED indicates unit is connected and receiving power  
**Lightweight aluminum housing** about the size of a credit card for easy carrying in a backpack or

### Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-A ports provide up to 1.5A each for charging devices
- Supports true 10/100/1000 Mbps Ethernet network speeds
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

### System Requirements

- Source device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

### Package Includes

- U460-003-3A1GB USB 3.1 Gen 1 USB-C Portable Hub/Adapter, Black
- Quick Start Guide



laptop bag

**Connect USB Peripherals** 3 USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals Supports USB Battery Charging (BC) specification v1.2, so ports provide up to 1.5A for fast charging of mobile devices Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps Backward compatible with USB 2.0 and USB 1.1

**Access a Wired Gigabit Ethernet Network** RJ45 port supports true 10/100/1000 Mbps network speeds Recommended for a faster wired network connection or getting online when no Wi-Fi is available  
**Built-In Cable with Reversible USB-C Connector** Fumble-free reversible USB-C plug connects in either direction for quick connection every time

**Manufactured to Exacting Specifications** Compliant with IEEE 802.3az (Energy Efficient Ethernet) Supports IPv4 and IPv6 pack COE (Checksum Offload Engine) to reduce CPU loading Supports full- and half-duplex operations Supports Wake-on-LAN, jumbo frames and VLAN tagging

## Specifications

OVERVIEW	
UPC Code	037332213891
OUTPUT	
Charging Ports / Amps	(3) 1.5A
Charging Watts	7.5
INPUT	
Bus Powered	Yes
Product Length (in.)	12
Product Length (cm.)	30.48
Product Length (ft.)	1
Product Length (m.)	0.3
BATTERY	
Battery Charging (1.2 Port)	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White LED indicates power
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Weight (lbs.)	0.00
Unit Dimensions (hwd / in.)	0.84 x 3.8 x 1.2



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	3.2 BTU/Hr
Power Consumption (Watts)	0.95
Power Provided to Connected Device(s)	Up to 5V 1.5A (7.5W) per USB Port
<b>COMMUNICATIONS</b>	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3u; 802.3ab; 802.3az
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	N201-Series Cat6 Gigabit Snagless Patch Cables
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Technology	Cat5/5e; Cat6; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); USB
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>