

MU10/14.5.SF1



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

General Information

Extended Product Type:	MU10/14.5.SF1
Product ID:	1SNA199011R1600
EAN:	3472591990119
Catalog Description:	MU10/14.5.SF1 Screw Clamp Terminal Blocks - For 5 x 20 and 5 x 25 fuses - Black
Long Description:	- Protect your circuits with 5x20 and 5x25 fuse terminal blocks (fuse not supplied with terminal blocks), - Closed terminal block: no end section needed, optimized rigidity.

Ordering

Color:	Black
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-A screw clamp
Instructions and Manuals:	1SNC160001C0207-CH-A screw clamp

Dimensions

Product Net Width:	14.5 mm
Product Net Height:	78 mm
Product Net Depth / Length:	76 mm
Product Net Weight:	60 g

Technical

Rated Cross-Section:	10 mm ²
Spacing:	14.5 mm
Connection Type:	Screw clamp
Function:	Fuse
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.5 ... 10 mm ² Screw Clamp / Rigid 1x 0.5 ... 16 mm ²
Rated Current (I_n):	Main Circuit 16 A
Rated Voltage (U_r):	750 V
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	12.0 mm
Recommended Screw Driver:	5.5 mm
Tightening Torque:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22 ... 10 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG
Flammability According to UL94:	V0

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Certificates and Declarations (Document Number)

CSA Certificate:	1SND161066A0201
cUL Certificate:	1SND161000A0203
Declaration of Conformity - CE:	1SND225016U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220021E1002
Instructions and Manuals:	1SNC160001C0207-CH-A screw clamp
RoHS Information:	1SND230023F0208

Classifications

Object Classification Code:	X
ETIM 4:	EC000899 - Fuse terminal block
ETIM 5:	EC000899 - Fuse terminal block
ETIM 6:	EC000899 - Fuse terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	172 mm
Package Level 1 Depth / Length:	155 mm
Package Level 1 Height:	71 mm
Package Level 1 Gross Weight:	1.2 kg
Package Level 1 EAN:	3472591990119

Package Level 2 Units: 200 piece

Package Level 3 Units: 4800 piece

Product Packing Type: Box

