

# Han DD double module, crimp male



Part number	09 14 036 3002
Specification	Han DD double module, crimp male
HARTING eCatalogue	https://b2b.harting.com/09140363002

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Modules
Series	Han-Modular <sup>®</sup>
Type of module	Han DD <sup>®</sup> module

#### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	36
Details	Please order crimp contacts separately.

## Technical characteristics

Conductor cross-section	0.14 2.5 mm²
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500
Mating cycles with other HMC components	≥10,000

## Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



## Material properties

Colour (insert) RAL 7032 (pebble grey)

Material flammability class acc. to UL 94 V-0

## Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

## Commercial data

Packaging size	1
Net weight	18 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440217 Module for industrial connectors (power/signals)