

# Product data sheet

## Characteristics

# LA1LC010

TeSys integral - auxiliary contact - 2 NO + 1 NC + 3C C/O

Product availability : Non-Stock - Not normally stocked in distribution facility



⚠ Discontinued

LA1LC010 has not been replaced. Please contact your customer care center for more information.

### Main

Range	TeSys
Device short name	LA1LC
Product or component type	Auxiliary contact

### Complementary

Range compatibility	TeSys Integral contactor breaker
Mounting location	Right side
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NO + 1 NC contactor state 1 C/O control knob in any position other than auto 1 C/O tripped 1 C/O tripped on short-circuit
[Ui] rated insulation voltage	690 V
[Ith] conventional free air thermal current	6 A
Connections - terminals	screw clamp terminals 2 0.00 in <sup>2</sup> (1.5 mm <sup>2</sup> ) screw clamp terminals 1 0.00 in <sup>2</sup> (2.5 mm <sup>2</sup> )
Net weight	0.62 lb(US) (0.28 kg)

### Environment

Environmental characteristic	Standard environment
------------------------------	----------------------

### Ordering and shipping details

Category	22384 - STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
GTIN	03389110180107
Returnability	No
Country of origin	CZ

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
------------------	-----------------------------------

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------