

PRODUCT-DETAILS

CL-502R

PILOT LIGHT CL-502R 24V a.c./d.c.



General Information

Extended Product Type	CL-502R
Product ID	1SFA619402R5021
EAN	7320500250280
Catalog Description	PILOT LIGHT CL-502R 24V a.c./d.c.
Long Description	Compact Pilot Light - Pilot light head - Red - Illuminated - Lamptype: LED 24V AC / DC

Ordering

E-Number (Sweden)	3711340
EAN	7320500250280
Minimum Order Quantity	10 piece
Customs Tariff Number	85369001

Dimensions

Product Net Width	0.03 m
Product Net Height	0.03 m
Product Net Depth / Length	0.055 m
Product Net Weight	0.022 kg

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	0.1 m
Package Level 1 Height	0.03 m
Package Level 1 Depth / Length	0.1 m
Package Level 1 Gross Weight	0.022 kg

Environmental

Ambient Air Temperature	Operation -25 ... +70 °C Storage -30 ... +85 °C
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Additional Information

Actuator Type	Pilot light head
Color	Red
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Illumination	Illuminated
Lamp Type	LED 24V AC / DC
Order Multiple	1 piece
Product Main Type	CL
Product Name	Pilot Light
Product Range	Compact
Product Type	CL
Rated Current (I_n)	15 mA
Rated Frequency (f)	Supply Circuit 50 60 Hz
Rated Operational Voltage	24 V AC/DC
RoHS Date	0626 5

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SFC151003C0201
Declaration of Conformity - CE	1SFA1-70
Environmental Information	1SFC151009D0201
Instructions and Manuals	1SFC151003C0201
RoHS Information	1SFC151012D0202

Classifications

ETIM 4	EC002024 - Accessories for control circuit devices
ETIM 5	EC002024 - Accessories for control circuit devices
Object Classification Code	E
UNSPSC	39121500

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Compact Range

