



Catalog Number: TY400-50-ANTI
Product ID: 7TAG054970R0002
UPC Number: 78621008514
EAN Number: 05415022436242
Status: A

Antimicrobial Treated Cable Tie, Ivory Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/2S Rated for AH-2 Plenum, Length of 363mm (14.3 Inches), Width of 4.7mm (0.186 Inch), Thickness of 1.5mm (0.059 Inch), Tensile Strength Rating of 220 Newtons (50 Pounds), Minimum Bundle Diameter 1.5mm (0.059 Inch), Maximum Bundle Diameter 102mm (4.02 Inches)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Antimicrobial
Width	0.186 in ; 4.7 mm
Length	14.3 in ; 363 mm
Thickness	0.059 in ; 1.5 mm
Bundle Diameter	0.059 to 4.02 in ; 1.5 to 102 mm
Material	Nylon/Polyamide 6.6
Color	Ivory
Lock Mechanism	Plastic Pawl
Tensile Strength	50 pounds ; 222 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.7mm
Length belt/tape/tie	363mm
Tie thickness	1.5mm
Max. bundle diameter	102mm
Min. holding force	222N
Operating temperature	-60-+85°C
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Other
Halogen free	Y
Colour	Cream
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	100
Inner Dimensions (inches)	19x5x1.5
Outer Quantity	1000
Outer Dimensions (inches)	16.12x8x6.87
Weight Uom	5.49 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001570
Marketing Brochure US	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com