

Ball valve
QH-1 1/2
Part number: 6837

FESTO



Data sheet

Feature	Value
Type code	QH
Nominal pressure of fitting PN	30
Valve function	2/2 bistable
Pneumatic connection 1	G1 1/2
Pneumatic connection 2	G1 1/2
Actuation type	Manual
Type of mounting	Line installation
Standard nominal flow rate	84000 l/min
Nominal width	40 mm
Ambient temperature	-20 °C ... 180 °C
Housing material	Brass
Operating medium	Water Compressed air as per ISO 8573-1:2010 [7:-:-]

Feature	Value
Sealing principle	Soft
Design	Ball valve
Symbol	00991458
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)