


Hand slide valve VBOH-32-G14

Part number: 1302994

FESTO



Data sheet

Feature	Value
Type code	VBOH
Valve function	3/2, bistable
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Actuation type	Manual
Type of mounting	Line installation Screw-in
Standard nominal flow rate	1675 l/min
Nominal width	8.4 mm
Operating pressure	-0.95 bar ... 12 bar
Ambient temperature	-10 °C ... 80 °C
Housing material	Anodized Wrought aluminum alloy
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Width dimension	31 mm
Sealing principle	Soft
Mounting position	Any
Design	Sleeve gate valve
Type of control	Direct
Flow direction	Reversible
Symbol	00991286
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-10 °C ... 80 °C
Actuating force	45 N
Product weight	35 g
Material of screwed trunnion	Wrought aluminum alloy Anodized
Note on materials	RoHS-compliant
Seals material	NBR