

### OPERATION

The CMG Series is a self powered Current Monitor/Relay that is used to detect the presence of AC current. When the monitored current exceeds the trip point for longer than 400 mSec., the internal relay energizes (Pick-up). When the monitored current drops below the trip point for longer than 50 mSec., the internal relay de-energizes (Drop-out). No physical connection is required as the line to be monitored is magnetically coupled by passing the conductor through the protruding Current Transformer of the monitor. No external supply is needed to power the monitor.


The current trip point specified is with one turn through the transformer. Each time the number of turns through the transformer doubles, the trip point effectively halves. Example: CMG-0100-20 will trip at 20 amps with one turn passing through the transformer. By placing two turns through the transformer, the relay will trip at 10 amps. Likewise, four turns will cause the relay to trip at 5 amps. (See below)



### DIMENSIONS (INCHES)



## WIRING







# AC Self Powered Go/No-Go **Current Monitor/Relays**

- · No physical connection to the AC line that is being monitored
- · Magnetically coupled by passing supply line through protruding **Current Transformer**
- Withstands 400 Ampere-Turns Continuous
- · No supply voltage required
- Will operate on 24, 120, 240 or 480 VAC lines
- 1/4" Quick Disconnect Terminals

### **SPECIFICATIONS**

CONTROL VOLTAGE	Not Required		
TRIP POINTS	Pick-up Drop-out	See Order Information 25% below Pick-up	
	Diop-out	23 /6 below rick-up	
OUTPUT	SPST - N/0, 5 Amps @ 240 VAC, Res.		
	(Available as request #CN	s a normally closed contact upon 1G-0200)	
HYSTERESIS	25%		
RESPONSE TIME	Operate	400mSec. (Approximately)	
	Release	50mSec.	
ACCURACY	±5% on Pick-up		
<b>TERMINATIONS</b>	(2) 1/4" Quick Disconnect Terminals		
RESET	Automatic		
TEMPERATURE	Operate	32° to 131°F (0° to +55°C)	
RATING	Storage	-49° to 185°F (-45° to +85°C)	
ENCLOSURE	Style "D" Surface Mounted		
WEIGHT	4 oz.		

#### **MODEL NUMBER**

MODEL NUMBER	CMG	0100	
CURRENT TRIP POINTS			
20 amps			20
24 amps			24
28 amps			28
32 amps			32
36 amps			36

**CURRENT MONITORS**