



Specification

Filter type	C
Capacitance	3900pF±20%
Working Voltage	100V
Current rating	6.5 A

Minimum Insertion Loss

FREQUENCY (MHz)	ATTENUATION dB
1	1dB
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB

Notes

Screws are not pre-mounted to allow mounting from any ends

<p>All Dimensions in mm Original Size DIN A 4</p>	Techn. Character.			Free size tolerances		
		Dat.	Name	Scale	Male/Female D-Sub Filter Adapter 15pin, 3900pF	
		Detail.	03.09.07			J.S.
		Insp.	03.09.07			J.S.
	Stand.			1:1		
Mod.	Dat.	Name	Zhuhai HARTING Limited			
					TB 09 64 200 7240	
			Sub.		Page	