



Main

Range	TeSys
Product or component type	Electrical remote stop
Device short name	LAD
Accessory / separate part category	Electrical accessory
Product compatibility	LRD313...LRD365 LRD01...35 LR3D01...D35 LR3D313...LR3D365
[Uc] control circuit voltage	415/440 V AC 50/60 Hz

Complementary

Maximum inrush power in VA	100 VA
Net weight	0.09 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------