



2.8MM 4K LENS TURRET CAMERA

FEATURES:

- Up to 8 Megapixel high resolution
- 2.8mm 4K lens
- 25-30m IR Distance
- DC12V
- 36pcs IR LED
- IP66 weather-proof protection

Model No.	4K-TUR-FG36 / 4K-TUR-FW36
Image Sensor	1/2.3" colour CMOS 4K image sensor
Signal System	PAL/NTSC
Active Pixels	3840(H)x2160(V)
Lens	2.8mm 4K lens
Angle of View	H:105°
Horizontal Resolution	4K (8MP)
Backlight	BLC/Off
Sharpness	Low/Middle/High
Min Illumination	0 Lux (IR ON - IR-cut technology)
Menu	UTC Control (or OSD cable)
Language	ENG/CHN/GER/FRA/ITA/SPA/POL/RUS/POR/NED/TUR/JPN
Shutter	FLK/Auto
Day/Night	Ext/Auto/Colour/B&W
White Balance	ATW/ATW->SET
3DNR	Low/Middle/High
Mirror	Mirror/V-Flip/Rotate/Off
Brightness	0-100 (LSC: On/Off)
Video Output	TVI / AHD / CVI / CVBS ** Factory Default is TVI
Power Supply	DC12V $\pm$ 10%
Current Consumption	130 mA(IR OFF), 370 mA(IR ON)
IR Led	36 pcs
IR Distance in Effect	25-30M
IP Rating	IP66
Storage Temperature	-50°C ~ +90°C
Operating Temperature	-30°C ~ +70°C
Dimension	Φ120*86mm
Weight	800g

DIAGRAM:

