

Wired Microphone | USB | Black/Grey

General information

With this high quality, sensitive USB microphone you're assured of clear voice recording, due to the Noise Cancelling function. No more inconvenient background noise! The flexible tube allows the user to direct it any way he or she wants. It is possible to adjust the volume control and it features Plug & Play. The 3.5 mm Jack connector on the microphone can be used to connect a headset.

Features

- On/off button
- Mute button
- 360 Degrees directional
- Flexible tube
- Plug & Play
- Compliant with: USB2.0/1.1
- Directivity: Noise Cancelling
- Impedance: 2.2k ohm

Specifications

Cable length:	1.5 m
Impedance:	2200 Ohm
Sound pressure level:	100 dB
Sensitivity:	-46 dB
Frequency characteristic:	100 Hz... 10 kHz
Signal-to-noise ratio:	50 dB
Number of microphones included:	1
Colour:	Black/Grey
Material:	Plastic / Aluminium
On/off switch:	Yes / Mute
Appliance:	Desktop
Appliance:	Notebook
Output connectors:	USB
Power plug:	USB
Connection output:	USB A Male



Sales information

Order code:	MICDU100BK
Product description:	Wired Microphone USB Black/Grey
Packaging:	Blister
Brand name:	Nedis



Quantity	LxWxH (mm)	Weight
1	137x360x35	210 gr.
20	370x290x350	4960 gr.



Wired Microphone | USB | Black/Grey

Connection: Wired

Package contents

Microphone