

PRODUCT-DETAILS

CP-AF20A

ADAPTAFLEX CONTRACTOR PACK



General Information

Extended Product Type	CP-AF20A
Product ID	7TCA296180R0006
EAN	5020963000300
Catalog Description	ADAPTAFLEX CONTRACTOR PACK
Long Description	Convenience Pack, Nylon Conduit with Adaptalok One-Piece, Fast Fit, Push & Twist Conduit Fittings, Conduit / Conduit Fitting Diameter 20mm, 10 One-Piece Conduit Fittings, 10 Locknuts, IP66 Rating, Black

Ordering

EAN	5020963000300
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	1.59 lb 721.088 g
--------------------	----------------------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	37 in 940 mm

Package Level 1 Height	17 in 432 mm
Package Level 1 Depth / Length	17 in 432 mm
Package Level 2 Units	10 piece
Package Level 2 Width	37 in 940 mm
Package Level 2 Height	17 in 432 mm
Package Level 2 Depth / Length	17 in 432 mm

Additional Information

Application	Convenience Pack with Conduit, Fittings, and Locknuts
Brand / Label	Adaptaflex
Color	Black
Insulation Material	IP66
Material	Nylon
Number of Batteries	0
Product Name	PLASTIC CONDUIT WITH FITTINGS
Product Type	Contractor Convenience Pack
Size	20mm Conduit and Fitting
UPC	786210303659

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	CP-AF20A
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	CP-AF20A

Classifications

UNSPSC	39121421
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4586 >> Electrical connector assembly

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

