

PRODUCT-DETAILS

AL21/M20/A/BL

ADAPTALOK 21MM M20 THREADSTRAIGHT F



General Information

Extended Product Type	AL21/M20/A/BL
Product ID	7TCA296000R0585
EAN	5020963000164
Catalog Description	ADAPTALOK 21MM M20 THREADSTRAIGHT F
Long Description	Straight Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 21mm, M20 Thread, Black

Ordering

EAN	5020963000164
Customs Tariff Number	3917400090

Dimensions

Product Net Weight	.029 lb 13.152 g
--------------------	---------------------

Container Information

Package Level 1 Units	10 piece
Package Level 2 Units	200 piece
Package Level 2 Width	14 in 356 mm

Package Level 2 Height	6 in 152 mm
Package Level 2 Depth / Length	14 in 356 mm

Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Brand / Label	Adaptaflex
Cable Entry Position	M20 Thread
Color	Black
Material	Polyamide/Nylon 6.6
Number of Batteries	0
Product Name	PLASTIC FITTING FOR CONDUIT
Product Type	Conduit Fitting with Metric Threads
Size	NC 21mm
UPC	786210279749

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	AL21/M20/A/BL
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	AL21/M20/A/BL

Classifications

ETIM 6	EC001176 - Screw connection for corrugated plastic hose
ETIM 7	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

