

PRODUCT-DETAILS

# SP16/BL/10M

## 10M X SP16/BLACK CONDUIT



### General Information

Extended Product Type	SP16/BL/10M
Product ID	7TCA296020R0077
EAN	5020963001130
Catalog Description	10M X SP16/BLACK CONDUIT
Long Description	Liquid Resistant, General Purpose, Highly Flexible Conduit, Nominal Conduit Size 16mm, Outside Diameter 17.0mm, Inside Diameter 13.0mm, Static Bend Radius 35mm, Reel Length 10 Meters, PVC Jacket with Galvanised Steel Core, Black

### Ordering

EAN	5020963001130
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	20.26 lb 9.188 kg
--------------------	----------------------

### Container Information

Package Level 2 Units	6 piece
Package Level 2 Width	37 in 940 mm

Package Level 2 Height	17 in 432 mm
Package Level 2 Depth / Length	17 in 432 mm

## Additional Information

Application	Indoors / Outdoors - Light Industrial, General Purpose, Buildings
Brand / Label	Adaptaflex
Color	Black
Flexibility	High
Inside Diameter	13.0 mm
Material	Galvanized Steel Core with PVC Jacket
Nominal Size	3/8 in 16 mm
Number of Batteries	0
Outside Diameter	17.0 mm
Product Name	STEEL FLEX ELECT.CONDUIT PVC JACKET
Product Type	High Flexibility Conduit
Radius	35 mm
UPC	786210239897

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SP16/BL/10M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SP16/BL/10M

## Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

