

PRODUCT-DETAILS

SP32/BL/10M

10M SP32/BLACK CONDUIT



General Information

Extended Product Type	SP32/BL/10M
Product ID	7TCA296020R0222
EAN	5020963000362
Catalog Description	10M SP32/BLACK CONDUIT
Long Description	Liquid Resistant, General Purpose, Highly Flexible Conduit, Nominal Conduit Size 32mm, Outside Diameter 34.0mm, Inside Diameter 28.1mm, Static Bend Radius 60mm, Reel Length 10 Meters, PVC Jacket with Galvanised Steel Core, Black

Ordering

EAN	5020963000362
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	13.56 lb 6.15 kg
--------------------	---------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	13 in 330 mm

Package Level 2 Height	7.55 in 192 mm
Package Level 2 Depth / Length	13 in 330 mm

Additional Information

Application	Indoors / Outdoors - Light Industrial, General Purpose, Buildings
Brand / Label	Adaptaflex
Color	Black
Flexibility	High
Inside Diameter	28.1 mm
Material	Galvanized Steel Core with PVC Jacket
Nominal Size	1 in
Number of Batteries	0
Outside Diameter	34.0 mm
Product Name	ADAPTAFLEX
Product Type	High Flexibility Conduit
Radius	60 mm
UPC	786210259321

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SP32/BL/10M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SP32/BL/10M

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

