



PRODUCT-DETAILS

SAMHL50/25M

50MM GALV CORE ANTI MICRO COND 25M



General Information

Extended Product Type	SAMHL50/25M
Product ID	7TCA296030R0451
EAN	5020963801600
Catalog Description	50MM GALV CORE ANTI MICRO COND 25M
Long Description	Liquidtight. Anti-Microbial Conduit, Conduit Size - Metric 50 Millimeters / US Trade Size 1-1/2 Inch, Outside Diameter 47.5mm, Inside Diameter 40.4mm, Static Bend Radius 240mm, IP40-IP69 Rating, Galvanised Steel Core with Thermoplastic Jacket, Reel Length 25 Meters, White

Ordering

EAN	5020963801600
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	82.04 lb 37.206 kg
--------------------	-----------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Suitable for indoor splash zone areas or food processing equipment
Brand / Label	Adaptaflex
Color	White
Flexibility	High
Inside Diameter	40.4 mm
Material	Galvanised Steel Core, String Packed and Thermoplastic Jacket
Nominal Size	50 mm
Number of Batteries	0
Outside Diameter	47.5 mm
Product Name	FLEXIBLE METAL CONDUIT
Product Type	Anti-Microbial Conduit
Radius	240 mm
UPC	786210213064

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SAMHL50/25M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SAMHL50/25M

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

