

PRODUCT-DETAILS

SPL16/M16/SAM

SS M16 FITTING FOR SAMHL16 CON



General Information

Extended Product Type	SPL16/M16/SAM
Product ID	7TCA296120R0043
EAN	5020963803871
Catalog Description	SS M16 FITTING FOR SAMHL16 CON
Long Description	Single Piece Conduit Fitting for Food and Beverage, Straight, Nominal Conduit Size 16mm, M16 Thread, 316 Stainless Steel

Ordering

EAN	5020963803871
Customs Tariff Number	7307290030

Dimensions

Product Net Weight	.22 lb 99.773 g
--------------------	--------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1.25 in 32 mm
Package Level 2 Height	1.25 in

	32 mm
Package Level 2 Depth / Length	1.3 in 33 mm

Additional Information

Application	Indoor Splash Zone Areas or Food Processing Equipment
Brand / Label	Adaptaflex
Cable Entry Position	M16 Thread
Color	Metallic
Material	Stainless Steel
Number of Batteries	0
Product Name	SS LIQUID TIGHT CONDUIT FITTINGS
Product Type	Liquid Tight Non-Metallic Fitting
Size	NC 16mm
UPC	786210291208

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SPL16/M16/SAM
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SPL16/M16/SAM

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

