

PRODUCT-DETAILS

FLH0530

LT-H FLEXIBLE CONDUIT 25MM 30M



General Information

Extended Product Type	FLH0530
Product ID	7TCA297020R0146
EAN	5011949202979
Catalog Description	LT-H FLEXIBLE CONDUIT 25MM 30M
Long Description	Liquid Tight, High Temperature Conduit, Nominal Conduit Size 25mm, 3/4 Inch US Trade Size, Outside Diameter 26.4mm, Inside Diameter 21.0mm, Static Bend Radius 110mm, Reel Length 30 Meters, Galvanised Steel Core, String Packing with Thermoplastic Rubber Covering, Black

Ordering

EAN	5011949202979
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	39.72 lb 18.014 kg
--------------------	-----------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Extreme Temperature Environments
Brand / Label	Kopex
Color	Black
Flexibility	High
Inside Diameter	21.0 mm
Material	Galvanized Steel Core with String Packing and Thermoplastic Rubber Coating
Nominal Size	3/4 in NC25
Number of Batteries	0
Outside Diameter	26.4 mm
Product Name	flex metal conduit
Product Type	Liquid Tight High Temperature Conduit
Radius	110 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210276649

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FLH0530
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	FLH0530

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

