

PRODUCT-DETAILS

XMM0505

KFC STR CONNECTORS 25X25MM



General Information

Extended Product Type	XMM0505
Product ID	7TCA297020R0471
EAN	5011949209152
Catalog Description	KFC STR CONNECTORS 25X25MM
Long Description	Liquid Tight Fitting for Covered Conduit, Straight with External Male Thread, Conduit Size 25mm, M25 Thread, Very High Mechanical and UV Protection, IP66, IP67 Ratings, Nickel Plated Brass with PVC Sleeve and Nylon Inserts

Ordering

EAN	5011949209152
Customs Tariff Number	7412200090

Dimensions

Product Net Weight	.17 lb 77.098 g
--------------------	--------------------

Container Information

Package Level 1 Units	10 piece
Package Level 2 Units	150 piece
Package Level 2 Width	13 in

	330 mm
Package Level 2 Height	7 in 178 mm
Package Level 2 Depth / Length	13 in 330 mm

Additional Information

Application	For Insertion Into Threaded Entries & Knockouts Using a Locknut to Secure
Brand / Label	Kopex
Color	Metallic
Insulation Material	IP66, 67 Rating
Material	Brass with Nylon Inserts and PVC Sleeve
Number of Batteries	0
Product Name	BRASS FITTING FOR CONDUIT
Product Type	Straight Swivel Fitting with External Thread for Covered Conduit
Size	Conduit Size 25mm ; M25 Thread
Special Functions	Very High UV Protection and Mechanical Protection
Standards	UL E60625, BSI Kitemark KM-90009, Low Voltage Directive
Surface Finishing	Nickel Plated
UPC	786210264462

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	XMM0505
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	XMM0505

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4585 >> Liquid tight connectors

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

