

PRODUCT-DETAILS

GFMS0404

KFE STR CONNECTOR 20X20MMSTAINLESS



General Information

Extended Product Type	GFMS0404
Product ID	7TCA297070R0046
EAN	5011949221437
Catalog Description	KFE STR CONNECTOR 20X20MMSTAINLESS
Long Description	Fitting for Uncovered Conduit, Straight with External Male Thread, Conduit Size 20mm, M20 Thread, Very High Mechanical and UV Protection, IP40 Rating, Stainless Steel AISI 316L

Ordering

EAN	5011949221437
Customs Tariff Number	7307221000

Dimensions

Product Net Weight	.31 lb 140.59 g
--------------------	--------------------

Container Information

Package Level 1 Units	1 piece
Package Level 2 Units	300 piece
Package Level 2 Width	14 in

	356 mm
Package Level 2 Height	16 in
	406 mm
Package Level 2 Depth / Length	14 in
	356 mm

Additional Information

Application	For Insertion Into Threaded Entries and Knockouts Using a Locknut to Secure
Brand / Label	Kopex
Color	Metallic
Insulation Class	IP40
Material	Stainless Steel AISI 316L
Number of Batteries	0
Product Name	stainless steel fitting for conduit
Product Type	Metallic Fitting for Uncovered Conduit
Size	Conduit Size 20mm ; M20 Thread
Special Functions	Very High Mechanical and UV Protection
Standards	BSI Kitemark KM-90009, Low Voltage Directive
Temperature Range	Static: -50 to 350 °C Dynamic: -45 to 250 °C
UPC	786210277103

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GFMS0404
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	GFMS0404

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

