

PRODUCT-DETAILS

# EXQM0304

## EXE LT STR 16MM FTNG N/P BR M20



Product image  
not available

### General Information

Extended Product Type	EXQM0304
Product ID	7TCA297120R0192
EAN	5011949001275
Catalog Description	EXE LT STR 16MM FTNG N/P BR M20
Long Description	Connector for Liquid Tight Conduit, Straight, Conduit Size 3/8 Inch/16mm, Thread Size M20, For Use in Industrial and Zone 2 Applications, IP66-67 Rating, Nickel Plated Brass

### Ordering

EAN	5011949001275
Customs Tariff Number	7412200035

### Dimensions

Product Net Weight	.12 lb 54.422 g
--------------------	--------------------

### Container Information

Package Level 1 Units	2 piece
Package Level 2 Units	10 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

## Additional Information

Application	For Use in Industrial and Zone 2 Applications to Connect Conduit Systems
Brand / Label	Kopex
Color	Metallic
Insulation Material	IP66, 67 Rating
Material	Brass
Number of Batteries	0
Product Name	brass fitting for conduit
Product Type	Straight Connector for Liquid Tight Conduit
Size	Conduit Size 16mm ; M20 Thread
Standards	BS EN 61386
Surface Finishing	Nickel Plated
Temperature Range	-50 to 130 °C
UPC	786210288550

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXQM0304
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXQM0304

## Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4585 >> Liquid tight connectors

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available