

PRODUCT-DETAILS

# EXLT0410

## LFH FLEXIBLE CONDUIT NC20 10M BLK



### General Information

Extended Product Type	EXLT0410
Product ID	7TCA297120R0136
EAN	5011949001947
Catalog Description	LFH FLEXIBLE CONDUIT NC20 10M BLK
Long Description	Liquid Tight Metallic Conduit, Low Fire Hazard, Conduit Size 20mm, Minimum Bore 16mm, Reel Length 10 Meters, Galvanised Steel Core with LFH Coating, Black

### Ordering

EAN	5011949001947
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	8.63 lb 3.914 kg
--------------------	---------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm
Package Level 2 Height	1 in

	25 mm
Package Level 2 Depth / Length	1 in
	25 mm

---

### Additional Information

Application	Connection for Conduit Systems when Low Fire Hazard is Needed
Brand / Label	Kopex
Color	Black
Inside Diameter	16 mm
Material	Galvanized Steel Core with Low Fire Hazard Coating
Nominal Size	20 mm
Number of Batteries	0
Product Name	KOPEX
Product Type	Liquid Tight Metallic Conduit
Special Functions	Limited Fire Hazard, Zero Halogen (BS6425 Pt1)
Standards	LUL compliant (E1042A6)
UPC	786210264318

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXLT0410
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXLT0410

---

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

