



### **Main Features**

Protective Safety Features: Prevents damage to both the car battery and the appliance plugged in.

Flexible Design: Adjustable positioning whatever the vehicle.

Compact and Lightweight: Easily stored within your vehicle.

Functional: Suitable for both professional and personal use.

Spring Tension Switch: Accommodates different sized cigarette lighter sockets.

### **Specification**

Maximum power rating 75 watts (5 mins)

Continuous power rating 56 watts (4 hours)

Surge capacity 150 watts

Standby current 0.1 amps

Nominal voltage 12 volts DC

Efficiency 90%

Output Modified sine wave

Part number RINV75

Barcode 5011274007508

Boxed outer qty. 20 x 1

The MP:75 Mininverter is and marked

### **Typical applications Watts**

Mobile phone charger 5W – 10W

Camcorder charger 3W – 20W

Video game console 39W – 100W

Portable work light 8W – 60W

Portable stereo system 10W – 40W

Laptop computer 60W – 90W

Palm Top computer 56W – 70W

Digital camera charger 3W – 19W