

9319



These devices are the simplest solution for SVGA and VGA signal distribution. By cascading them an infinite number of monitors displaying the same image can be achieved. These standard resolution splitters cater for monitors with bandwidths up to 250 Mhz. The distribution units incorporate signal boosters which enhance the video signal for long distance broadcasting; up to 35m.

Features:

- Enhances signal strength between 1 video input to 2, 4 or 8 video outputs
- Resolution levels: VS-102 & VS-104 up to 1600 x 1200 @ 70 Hz, VS-108 up to 1600 x 1200 @ 60 Hz
- Bandwidth: 250 MHz (VS-102, VS-104), 200 MHz (VS-108)
- Transmission Distance: up to 35m (using gain picture switch for best quality)
- Range is suitable for SVGA, VGA, Multisync monitors with cascading feature
- **Connectors:**
- IN from PC: High Density 15 D type Male
- OUT from Device: High Density 15 D type Female