

## Coaxial Cable Connector 24\_SMA-50-2-45/133\_N

### Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0047 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Catalogue drawing	DCA-00008868
Assembly instruction	DOC-0000179078
Mounting hole	DOU-00008748

### Ordering Information

Bulk 100 pcs package	24_SMA-50-2-45/133_NH
Single package	24_SMA-50-2-45/133_NE

### Additional Information

Suitable cables	K_02252_D, ENVIROFLEX_316_D, G_02232_D
-----------------	--