

MANUAL WIRE WRAPPING TOOLS & KITS

MANUAL WIRE WRAPPING TOOLS



G100/R3278INS
(Shown with Bit/Sleeve)

G200/R3278 Lexan™
G100/R3278 Aluminum

The G100/R3278 and G200/R3278 tools are designed with a chuck nose piece to make use of the full line of bits and sleeves made for power tools. The G100/R3278INS is coated with an insulative material, providing 1000V of dielectric strength across most of the housing, to help ensure worker and system safety. These tools accommodate wire sizes from 22 AWG (0.65mm) thru 32 AWG (0.20mm).

- G200/R3278 : Lexan™
- G200/R3278-K : Speed Wrap Tool kit
- G100/R3278 : Aluminum
- G100/R3278INS : Aluminum (insulated)
- For Bits & Sleeves : see page 11

MANUAL WIRE UNWRAPPING TOOL

The combination of the G100/R3394 unwrap tool and the SU unwrap bits gives you the best tool for high speed wire unwrapping. High production, long life, low maintenance. Use Unwrap Set SU2026 for wire AWG 20 thru 26 (0.80 thru 0.40mm) and Set SU2832 for wire AWG 26 thru 32 (0.40 thru 0.20mm).



G100/R3394

- G100/R3394 : Manual Wire Unwrapping Tool

G100/R3394 Bits & Sleeves:

Unwrap Bit Part No.	Unwrap Sleeve Part No.	Bit and Sleeve Set No.	Wire Size		Terminal Hole Diameter	
			AWG	mm	Inches	mm
2026UB	2032	SU2026	22-26	0.65-0.40	.070	1.77
2832UB	2032	SU2832	26-32	0.40-0.20	.036	0.96

TELECOM WIRE WRAP KIT



WWK-1

This is a complete kit for technicians working at a Main Distributing Frame. The G200/R3278 Manual Gun produces wire wrapped connections merely by squeezing the trigger, and works with any bit and sleeve. The versatile HW-UW-224 Hand Wrap-Unwrap Tool (22-24 AWG) does the work of two tools in one - wrapping and unwrapping - just by changing the cap from one end to the other. The ST-100 22-24 AWG wire Cut-and-Strip Tool offers easy, clean stripping of up to four wires with 15/16" - 19/16" adjustable strip off length. This kit comes complete with KB224 22-24 AWG bit, P2224 22-24 AWG sleeve and H-1000 cordura tool pouch.

- WWK-1 : Telecom Wire Wrap Kit