

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2149211123

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead PicoBlade Female-to-Pigtail, Tin Plated, 225.00mm Length, 28 AWG, Red



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	214921
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	PicoBlade
UPC	193264502646
Physical	
Cable Length	225.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.330/g
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.889µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.04mm max.
Wire Size AWG	28
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2149211121-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ECHA_01_2020 (16 January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

214921 Series

Use With

51021 PicoBlade Crimp Housing

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION