

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2149202214](#)
Status: **Active**
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Gold Plated, 300.00mm Length, 26 AWG, Black

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	214920
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	PicoBlade
UPC	193264502509

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.699/g
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.380µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.04mm max.
Wire Size AWG	26
Wire/Cable Type	UL 1061

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	2149202221-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214920 Series](#)

Use With

[51021 PicoBlade Crimp Housing](#)