

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2149212125](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead PicoBlade Female-to-Pigtail, Gold Plated, 450.00mm Length, 28 AWG, Red

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|---|
| Product Family | Cable Assemblies |
| Series | 214921 |
| Assembly Configuration | Pre-crimped Lead Only |
| Connector to Connector | PicoBlade Crimp Terminals |
| Overview | Off-the-Shelf Pre-Crimped Leads |
| Product Name | PicoBlade |
| UPC | 193264502868 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 450.00mm |
| Circuits (Loaded) | 1 |
| Color - Resin | Red |
| Gender | Female-Pigtail |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Net Weight | 0.603/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.25mm |
| Plating min - Mating | 0.380µm |
| Single Ended | Yes |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.04mm max. |
| Wire Size AWG | 26 |
| Wire/Cable Type | UL 1061 |

Electrical

| | |
|-------------------------------|------------------|
| Current - Maximum per Contact | 1.0A |
| Voltage - Maximum | 125V AC (RMS)/DC |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2149212121-000 |
|---------------|----------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214921 Series](#)

Use With

[51021 PicoBlade Crimp Housing](#)