

## Fasteners



**Table clamp** for all magnifier, arm-mounted and flexible-tube luminaires

Colour	Special feature	Order No.
black	0 - 45 mm	190008019 - 00014923
black	0 - 65 mm	190007019 - 00014904
black	65 - 135 mm	190033019 - 00014950
black	95 - 165 mm	190035019 - 00014956
black	0 - 65 mm, ESD design	190007059 - 00058094



**Wall angle bracket** for MINELA, RING LED, ROCIA arm-mounted luminaires, ROCIA flexible-tube luminaires and ABLTL

Colour	Special feature	Order No.
black	-	300213018 - 00025178
white	-	300213038 - 00070291



**Wall bracket** for TANEQ, TEVISIO and SNLQ

Colour	Special feature	Order No.
black	-	226108019 - 00610754



**Wall bracket** for MINELA, SNLQ and RING LED

Colour	Special feature	Order No.
black	-	D13148000 - 00075404



**Magnetic base** for ROCIA pivoting-head luminaires

Colour	Special feature	Order No.
black	-	190057019 - 00015056



190037



190036

### Table base for MINELA and RING LED

Colour	Special feature	Order No.
light grey	-	190037159 - 00014993
black	-	190036039 - 00014959
light grey	-	190036119 - 00065399



### Additional angle bracket as an accessory for TAMETO for rotatable mounting of the side luminaire to the extension arm

Colour	Special feature	Order No.
black	adjustable	408001917 - 00561205



### Luminaire bracket for TAMETO for rotatable mounting to the extension arm

Colour	Special feature	Order No.
black	adjustable	408001899 - 00630199



### Luminaire bracket set for TAMETO for C-rails (pair)

Colour	Special feature	Order No.
black	adjustable	408001586 - 00578088



### Mounting frame for LUMATRIS

Colour	Special feature	Order No.
silver-grey	for luminaire size 246 x 95 mm	408001016 - 00595619
silver-grey	for luminaire size 420 x 95 mm	408001017 - 00595613
silver-grey	for luminaire size 596 x 95 mm	408001018 - 00595610
silver-grey	for luminaire size 770 x 95 mm	408001019 - 00595616
silver-grey	for luminaire size 420 x 170 mm	408001037 - 00518121
silver-grey	for luminaire size 770 x 170 mm	408001034 - 00514265



### Luminaire bracket set for LUMATRIS

Colour	Special feature	Order No.
silver-grey	for luminaire width 95 mm	408001015 - 00595587
silver-grey	for luminaire width 170 mm	408001035 - 00514268



### Pivoting head for LUMATRIS

Colour	Special feature	Order No.
silver-grey	adjustable	408001033 - 00514262



### Luminaire bracket for FLAT LED surface-mounted luminaire

Colour	Special feature	Order No.
-	adjustable	203081019 - 00019478



### Luminaire bracket set for MACH LED PLUS.forty

Colour	Special feature	Order No.
-	adjustable + / -90 °	408001403 - 00671626



### Luminaire bracket for MACH LED PLUS.forty\*

Colour	Special feature	Order No.
-	adjustable + / -20 °	408001402 - 00671623



### Luminaire bracket set for MACH LED PLUS.seventy

Colour	Special feature	Order No.
-	adjustable + / -65 °	408001876 - 00582065



**Luminaire bracket** for MACH LED PLUS.seventy \*

Colour	Special feature	Order No.
-	adjustable + / -30 °	408001878 - 00585535



**Luminaire bracket set** for RL 40

Colour	Special feature	Order No.
-	-	408001952 - 00459389



**Luminaire bracket** for RL 40 \*

Colour	Special feature	Order No.
-	-	306266022 - 00085912



**Luminaire bracket** for RL 40 \*

Colour	Special feature	Order No.
-	-	190174019 - 00092088



**Luminaire bracket** for MACH LED PLUS.seventy and RL 70 \*

Colour	Special feature	Order No.
-	with rubber profile	SK1021719 - 00085499



**Luminaire bracket** for MACH LED PLUS.seventy and RL 70 \*

Colour	Special feature	Order No.
-	with rubber profile	SK0995719 - 00085652



### Luminaire bracket for MACH LED PLUS.seventy and RL 70 \*

Colour	Special feature	Order No.
-	with rubber profile	190015719 - 00085498



### Luminaire bracket for RL 70 \*

Colour	Special feature	Order No.
-	-	190027019 - 00057337



### Luminaire bracket for AWD

Colour	Special feature	Order No.
black	-	191092019 - 00086727



### Luminaire bracket for TAUREO for fastening to the luminaire

Colour	Special feature	Order No.
-	wire for cable mounting	H13001010 - 00600389
-	stainless steel for direct mounting	H13001020 - 00600398
-	stainless steel for cable mounting	H13001030 - 00600395



### Wire rope for TAUREO and ACANEO

Colour	Special feature	Order No.
-	3 000 mm, hook for trapezoidal metal ceiling	H13003010 - 00604334
-	3 000 mm, M8 thread for trapezoidal hanger	H13003020 - 00604337
-	3 000 mm, snap link for eyebolts (ceiling)	H13003030 - 00604340
-	3 000 mm, hook for screw fixing (ceiling)	H13003040 - 00604343



### Wire rope holder for TAUREO and ACANEO

✉ Do you have any questions?

Colour	Special feature	Order No.
-	for cable diameter 1.5 mm / 2.0 mm / 2.5 mm	H13004010 - 00604354



**Trapezoidal hanger** for TAUREO and ACANEO for fastening to the trapezoidal sheet metal ceiling

Colour	Special feature	Order No.
-	with M8 thread	H13004020 - 00605752



**Luminaire bracket for ceiling mounting** for ACANEO

Colour	Special feature	Order No.
-	fixed	337818010 - 00695171
-	adjustable	337818020 - 00695174



**Luminaire bracket for wall mounting** for ACANEO

Colour	Special feature	Order No.
-	-	337763010 - 00682509



**1-point suspension (ceiling mounting)** for ACANEO

Colour	Special feature	Order No.
-	wire ropes will be required	337765040 - 00695279



**1-point suspension set (ceiling mounting)** for ACANEO

Colour	Special feature	Order No.
-	1 x 1-point suspension, 2 wire rope holder, 2 wire ropes with hooks	226234019 - 00701156

\* At least two brackets per luminaire required

**Do you have any questions?**

**Do you have any questions?**

Herbert Waldmann GmbH & Co. KG  
Peter-Henlein-Straße 5  
78056 Villingen-Schwenningen  
Deutschland  
sales.germany@waldmann.com  
Phone +49 7720 601 0  
Fax +49 7720 601 290