

Dinion™ Mono Cameras



- 1/3" CCD professional quality cameras
- Ready to use straight from the box
- Auto detection of lens type
- Lens wizard for easy back focus adjustment
- High sensitivity
- Advanced digital signal processing
- Outstandingly easy to use
- Suitable for indoor or outdoor use

- Ideal for 90% of applications
- Available in standard and high resolution versions

Lens not supplied

Order Code	430-8141	430-8153	430-8165	430-8177
Resolution (TVL)	380	380	570	570
Sensor	1/3 CCD	1/3 CCD	1/3 CCD	1/3 CCD
Lux Level	0.15	0.15	0.1	0.1
Shutter Speeds	1/50 to 1/50000	1/50 to 1/50000	1/50 to 1/50000	1/50 to 1/50000
Lens	CS-Mount	CS-Mount	CS-Mount	CS-Mount
Iris	EI/AI	EI/AI	EI/AI	EI/AI
Voltage/Power	10.8 to 39V dc	85 to 265V ac	10.8 to 39V dc	85 to 265V ac
Connector	BNC	BNC	BNC	BNC
Dimensions (HxWxD)	122 x 66 x 58	122 x 66 x 58	122 x 66 x 58	122 x 66 x 58

248156.383132

Supply Voltage	Order Code	Price Each
Medium Resolution		
12V dc/24V ac	430-8141	
230V ac	430-8153	
High Resolution		
12V dc/24V ac	430-8165	
230V ac	430-8177	