

Dinion™ Colour Cameras



- 1/3" CCD Professional quality cameras
- Ready to use straight from the box
- Auto detection of lens type
- Lens wizard for easy back focus adjustment
- Automatic black level feature, to enhance images
- Advanced digital signal processing
- Outstandingly easy to use

- Suitable for indoor or outdoor use
- Ideal for professional, commercial or industrial surveillance systems
- Available in standard and high resolution versions
- Nightsense™ enhances the low light sensitivity by a factor of 3 by switching from colour to monochrome, making it ideal for use during the day and also at night. (high resolution camera only)

Lens not supplied

Order Code	430-8189	430-8190	430-8207	430-8219
Resolution (TVL)	330	330	480	480
Sensor	1/3 CCD	1/3 CCD	1/3 CCD	1/3 CCD
Lux Level	0.6	0.6	0.9(0.3 NightSense)	0.9(0.3 NightSense)
Shutter Speeds	1/50 to 1/125000	1/50 to 1/125000	1/50 to 1/125000	1/50 to 1/125000
Lens	CS-Mount	CS-Mount	CS-Mount	CS-Mount
Iris	EI/AI	EI/AI	EI/AI	EI/AI
Voltage/Power	10.8 to 39V dc	85 to 265V ac	10.8 to 39V dc	85 to 265V ac
Connector	BNC	BNC	BNC	BNC
Dimensions (HxWxD)	122 x 66 x 58	122 x 66 x 58	122 x 66 x 58	122 x 66 x 58

248384.383134

Supply Voltage	Order Code	Price Each
Medium Resolution		
12V dc/24V ac	430-8189	
230V ac	430-8190	
High Resolution		
12V dc/24V ac	430-8207	
230V ac	430-8219	