

miniMEDIA Category 8 Keystone Panel



Our new Category 8 12 port patch panel is equipped with zinc die-cast fully shielded Category 8 keystone sockets. This high performance package brings 25GB performance to 10" connectivity and perfectly complements our ***miniMEDIA*** 10" SOHO range.

Features

- Supplied with 12 diecast fully shielded toolless Cat 8 keystone jacks (SEKje)
http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pId=345
- Transmission performance in compliance with the ANSI/TIA 568-C.2-1 specifications for Category 8 cabling systems (i. e. suitable for runs of 5 – 30 metres)
- Compliant with IEC60512-99-001 – suitable for use with IEEE 802.3at (PoE+) applications
- Suitable for 0.51 – 0.65 mm/ 22 – 24 AWG stranded and solid wire
- Designed to complement the full range of ***miniMEDIA*** Cabinets:
miniMEDIA Black Metal Cabinet:
http://www.tuk.co.uk/tuk_live/product_details.php?category_id=16&pId=235
miniMEDIA Oak Veneer Cabinet:
http://www.tuk.co.uk/tuk_live/product_details.php?category_id=16&pId=236
- Robust and high quality metal construction
- Supplied with cage nut set, cable ties and earth wire with fixing screw

Specifications

- Weight: 634g
- Dimensions: 255 x 44 x 41.6 mm (approx.)
- Colour:
Panel: black Keystones: silver
- Material:
 - Panel
Front: cold rolled steel sheet, 1.5mm thickness, painted black
Rear panel: nickel plated
 - Keystone jack:
Body: nickel-plated die-cast zinc
RJ45 contacts: 50µ"/1.27µm gold-plated phosphor bronze
IDC contacts: tin-plated phosphor bronze
Tape: copper foil

Packaging: Supplied as a kit of 10" panel and 12 keystones in labelled white carton

Commodity code: 851777090

EAN: 5055386507860