



Ironworker's Pliers, Aggressive Knurl, 9-Inch



Klein Tools Ironworker's Pliers have aggressive teeth for a strong grip when twisting, snipping and pulling soft annealed rebar tire wire. The knurled jaws aid in easy twisting and turning. These pliers feature a hook-bend in the handle for added grip and leverage. Unique handle tempering helps absorb the "snap" when cutting wire.

Specifications

Type:	Ironworker's Pliers	Special Features:	Spring Loaded
Overall Length:	9.29" (23.6 cm)	Material:	Steel
Nose Type:	Square	Jaw Length:	1.594" (4.1 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.625" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Knife Length:	0.781" (2 cm)
Joint Type:	Hot Riveted	Handle Color:	Black
Handle Finish:	Plain	Handle Length:	7.375" (18.7 cm)
Insulated:	No	Tether Capable:	No
Weight:	1.0 lb (0.5 kg)		