



Adjustable Screwdriver, #2 Phillips, 1/4-Inch Slotted



The Adjustable Length screwdriver features a shaft that adjusts within 4-Inch to 8-Inch (10 to 12 cm) for numerous length choices. The shaft is removable and reversible with a different tip on each end. Carry fewer tools with this versatile multi-length, multi-bit driver.

Specifications

Type:	Adjustable-Length Screwdriver	Tip Size:	#2 Phillips, 1/4" (6.4 mm) Slotted
Magnetic:	No	Shank Length:	4" to 8" (101.6 to 203.2 mm)
Insulated:	No	Handle Material:	Rubber
Handle Color:	Black	Adjustable Length:	4" to 8" (101.6 to 203.2 mm)
Overall Length:	13.375" (339.7 mm)	Weight:	0.70 lb (0.32 kg)