



Heavy Duty Bent Trimmer, Ambidextrous, 11-Inch



Soft blue handle with extra large bottom ring that allows the operator to cut for long periods of time without the usual cramping of the hands! Can be used right or left handed. Highly durable scissors that also provide a comfortable grip.

Specifications

Material:	Stainless Steel	Blade Curvature:	Straight
Blade Edge:	Standard	Blade Length:	4.75" (12.1 cm)
Blade Tip:	Standard	Blade Finish:	Chrome Over Nickel Plated
Handed:	Ambidextrous	Handle Material:	Molded Plastic
Handle Orientation:	Bent	Handled:	Right
Tension Adjustment:	Screw	Inside Ring Size:	2.125" (5.4 cm)
Overall Length:	11" (27.9 cm)	Overall Height:	0.625" (1.6 cm)
Overall Width:	3.625" (9.2 cm)	Weight:	7.8 oz (222 g)