



Nylon-Webbing Lanyard Adjustable 6.5 to 10-Foot



Specifications

Application: For Use in Positioning, Suspension, or Retrieval Systems. Can Also Be Used with a Deceleration Unit for Fall Arrest	Special Features: Convenient Adjustable Length
Overall Length: 6.5 to 10' (2 to 3.1 m)	Adjustable Length: 6.5 to 10' (2 to 3.1 m)
Included: Two Drop Forged Steel, Corrosion Resistant Klein-Lok® Locking Snap Hooks with 11/16" (1.7 cm) Throat Opening and 1" (2.5 cm) Wide Orange Nylon Webbing Impregnated with Resin	Weight: 2.25 lb (1 kg)